

REF . 0 260 63


ELECTRONIC EARTH LEAKAGE MODULES - DPX/DPX-I 630 - MOUNTED UNDERNEATH -LED -4P -400 A


Emballage (nombre number of units)	1
Volume (dm ³)	7
Poids (g)	3 055,00

Caractéristiques du produit
Earth leakage modules

- Can be fitted onto DPX³/DPX³-I 630
- Adjustable, sealable sensitivity: 0.03 - 0.3 - 1 - 3 A
- Adjustable, time delay: 0 - 0.3 - 1 - 3 s
- Test push-button
- Reset push-button
- Remote earth fault signalling contact
- Switch for mechanical tests (installation insulation test)
- Mounted underneath
- 230-500 V~

LED version

- Monitors the isolation state of the installation via a series of LEDs
- 4P
- In : 400 A

Caractéristiques générales
DPX³ 630 - earth leakage modules
Documentation associée
 **Catalogue pages & additional information**

- [Description page \(p.148\)](#)
- [DPX³ 160/250/630 & 1600](#)
- [DPX³ 630](#)

 **Installation & technical data**

- [EXB19026_CA_DPX3_125HP250HP_630_1600EN](#)

 **Installation instructions & related documents**

- [LE07066AC](#)