

CAT. N° 0 260 65



## ELECTRONIC EARTH LEAKAGE MODULES - DPX/DPX-I 630 - MOUNTED UNDERNEATH - 4P - 630 A

Pack (number of units)	1
Volume (dm <sup>3</sup> )	7
Weight (g)	3 097,00

### Product characteristics

#### Earth leakage modules

- Can be fitted onto DPX<sup>3</sup>/DPX<sup>3</sup>-I 630
- Adjustable, sealable sensitivity: 0.03 - 0.3 - 1 - 3 A
- Adjustable, time delay: 0 - 0.3 - 1 - 3 s
- Test push-button
- Reset push-button
- Remote earth fault signalling contact
- Switch for mechanical tests (installation insulation test)
- Mounted underneath
- 230-500 V~

#### Standard

- 4P
- In : 630 A

### General characteristics

#### DPX<sup>3</sup> 630 - earth leakage modules

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.148\)](#)
- [DPX<sup>3</sup> 160/250/630 & 1600](#)
- [DPX<sup>3</sup> 630](#)

#### Installation & technical data

- [EXB19026\\_CA\\_DPX3\\_125HP250HP\\_630\\_1600EN](#)

#### Installation instructions & related documents

- [LE07066AC](#)

#### Agreements & certificates of conformity

- [CCC-2005010307161816](#)