

CAT. N° 0 270 12


**MCCB - DRX 125 - THERMAL MAGNETIC - ICU 10 KA - 415 V~ - 4P - IN 25 A**

Pack (number of units)	1
Volume (dm <sup>3</sup> )	1,53
Weight (g)	1 093,00

**Product characteristics**
**DRX 125**
**Breaking capacity Icu 10 kA (415 V~)**

- 4P
- 25 A

**General characteristics**
**DRX™ 125 - thermal magnetic MCCBs from 15 to 125 A**

- For switching, control, isolation and protection of low-voltage electrical lines
- Can be fitted with auxiliaries
- Supplied with:
  - M5 terminal for In ≤ 50 A and M8 range for In > 50 A
  - Fixing screws
  - Insulating shields (2 for 3P and 3 for 4P)
- Fixed thermal and magnetic
- Conform to IEC 60947-2, in compliance with NEMA

**Documentation**

**Catalogue pages & additional information**

- [Description page \(p.127\)](#)
- [Technical page \(p.128\)](#)
- [DRXTM 125](#)