

CAT. N° 0 271 10



MCCB - DRX 250 - THERMAL MAGNETIC - ICU 18 KA - 415 V~ - 4P - IN 225 A

Pack (number of units)	1
Volume (dm ³)	2,848
Weight (g)	1 851,00

Product characteristics

DRX 250

Breaking capacity Icu 18 kA (415 V~)

- 4P
- 225 A

General characteristics

DRX™ 250 - thermal magnetic MCCBs from 125 to 250 A

- For switching, control, isolation and protection of low-voltage electrical lines
- Can be fitted with auxiliaries
- Supplied with:
 - M8 terminals
 - Fixing screws
 - Insulating shields (2 for 3P and 3 for 4P)
- Fixed thermal and magnetic
- Conform to IEC 60947-2

Documentation



Catalogue pages & additional information

- [Description page \(p.129\)](#)
- [Technical page \(p.130\)](#)
- [DRXTM 250](#)



Environmental product profile

- [Environnemental product sheet n°20 E0227B-EN](#)



Agreements & certificates of conformity

- [OC / CB - SE 57104](#)