

CAT. N° 0 271 16



## MCCB - DRX 250 - THERMAL MAGNETIC - ICU 25 kA - 415 V~ - 3P - IN 225 A

Pack (number of units)	1
Volume (dm <sup>3</sup> )	2,121
Weight (g)	1 425,00

### Product characteristics

#### DRX 250

##### Breaking capacity Icu 25 kA (415 V~)

- 3P
- 225 A

### General characteristics

#### DRX™ 250 - thermal magnetic MCCBs from 125 to 250 A

- For switching, control, isolation and protection of low-voltage electrical lines
- Can be fitted with auxiliaries
- Supplied with:
  - M8 terminals
  - Fixing screws
  - Insulating shields (2 for 3P and 3 for 4P)
- Fixed thermal and magnetic
- Conform to IEC 60947-2

### Documentation



#### Catalogue pages & additional information

- [Description page \(p.129\)](#)
- [Technical page \(p.130\)](#)
- [DRXTM 250](#)



#### Installation & technical data

- [F00703EN05\\_DRX250](#)



#### Environmental product profile

- [Environnemental product sheet n°20 E0227B-EN](#)



#### Installation instructions & related documents

- [Y1393D](#)



#### Agreements & certificates of conformity

- [OC / CB - SE 57105](#)