

CAT. N° 0 271 23

**MCCB - DRX 250 - THERMAL MAGNETIC - ICU 25 KA - 415 V~ - 4P - IN 250 A**

Pack (number of units)	1
Volume (dm <sup>3</sup> )	2,848
Weight (g)	1 877,00

**Product characteristics****DRX 250****Breaking capacity Icu 25 kA (415 V~)**

- 4P
- 250 A

**General characteristics****DRX™ 250 - thermal magnetic MCCBs from 125 to 250 A**

- For switching, control, isolation and protection of low-voltage electrical lines
- Can be fitted with auxiliaries
- Supplied with:
  - M8 terminals
  - Fixing screws
  - Insulating shields (2 for 3P and 3 for 4P)
- Fixed thermal and magnetic
- Conform to IEC 60947-2

**Documentation****Catalogue pages & additional information**

- [Description page \(p.129\)](#)
- [Technical page \(p.130\)](#)
- [DRXTM 250](#)

**Environmental product profile**

- [Environnemental product sheet n°20 E0227B-EN](#)

**Agreements & certificates of conformity**

- [OC / CB - SE 57105](#)