

CAT. N° 0 271 62

**UNDERVOLTAGE RELEASE - FOR DRX - 48 V~/=**

Pack (number of units)	1
Volume (dm ³)	0,105
Weight (g)	49,00

Product characteristics**Control and signalling auxiliaries for DRX 125 and 250****Undervoltage releases**

- 48 V- and =

General characteristics**DRX™ 250 - thermal magnetic MCCBs from 125 to 250 A**

- For switching, control, isolation and protection of low-voltage electrical lines
- Can be fitted with auxiliaries
- Supplied with:
 - M8 terminals
 - Fixing screws
 - Insulating shields (2 for 3P and 3 for 4P)
- Fixed thermal and magnetic
- Conform to IEC 60947-2

Documentation**Catalogue pages & additional information**

- [Description page \(p.129\)](#)
- [Technical page \(p.130\)](#)
- DRXTM 250

**Installation instructions & related documents**

- [Y1217H](#)