

CAT. N° 0 271 63



UNDERVOLTAGE RELEASE - FOR DRX - 100/130 V~

| | |
|---------------------------|-------|
| Pack (number of units) | 1 |
| Volume (dm ³) | 0,105 |
| Weight (g) | 58,00 |

Product characteristics

Control and signalling auxiliaries for DRX 125 and 250

Undervoltage releases

- 110/130 V~

General characteristics

DRX™ 250 - thermal magnetic MCCBs from 125 to 250 A

- For switching, control, isolation and protection of low-voltage electrical lines
- Can be fitted with auxiliaries
- Supplied with:
 - M8 terminals
 - Fixing screws
 - Insulating shields (2 for 3P and 3 for 4P)
- Fixed thermal and magnetic
- Conform to IEC 60947-2

Documentation

Catalogue pages & additional information

- [Description page \(p.129\)](#)
- [Technical page \(p.130\)](#)
- DRXTM 250

Installation instructions & related documents

- [Y1217H](#)