

CAT. N° 0 271 73


CAGE TERMINALS - FOR DRX 100 - 4P - FROM 60 TO 100 A

Pack (number of units)	1
Volume (dm ³)	0,105
Weight (g)	65,00

Product characteristics
Connection accessories
Cage terminals

- 4P
- From 60 to 100 A

General characteristics
DRX™ 125 - thermal magnetic MCCBs from 15 to 125 A

- For switching, control, isolation and protection of low-voltage electrical lines
- Can be fitted with auxiliaries
- Supplied with:
 - M5 terminal for In ≤ 50 A and M8 range for In > 50 A
 - Fixing screws
 - Insulating shields (2 for 3P and 3 for 4P)
- Fixed thermal and magnetic
- Conform to IEC 60947-2, in compliance with NEMA

Documentation

Catalogue pages & additional information

- [Description page \(p.127\)](#)
- [Technical page \(p.128\)](#)
- DRXTM 125


Installation instructions & related documents

- [Y1217H](#)