

CAT. N° 0 271 80

**PADLOCK - FOR DRX - FOR LOCKING IN "OFF" POSITION**


Pack (number of units)	1
Volume (dm ³)	0,29
Weight (g)	29,00

Product characteristics**Padlock for DRX 125 and 250**

- For locking on "OFF" position (up to 3 locks)

General characteristics**DRX™ 250 - thermal magnetic MCCBs from 125 to 250 A**

- For switching, control, isolation and protection of low-voltage electrical lines
- Can be fitted with auxiliaries
- Supplied with:
 - M8 terminals
 - Fixing screws
 - Insulating shields (2 for 3P and 3 for 4P)
- Fixed thermal and magnetic
- Conform to IEC 60947-2

Documentation **Catalogue pages & additional information**

- [Description page \(p.127\)](#)
- [Technical page \(p.128\)](#)
- [Description page \(p.129\)](#)
- [Technical page \(p.130\)](#)
- [DRXTM 125](#)
- [DRXTM 250](#)