

CAT. N° 0 271 91



## SEALABLE TERMINAL SHIELDS (2) - FOR DRX 100 - 2P

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,701
Weight (g)	87,00

### Product characteristics

#### Connection accessories

##### Sealable terminal shields

- 2P
- Set of 2

### General characteristics

#### DRX™ 125 - thermal magnetic MCCBs from 15 to 125 A

- For switching, control, isolation and protection of low-voltage electrical lines
- Can be fitted with auxiliaries
- Supplied with:
  - M5 terminal for  $I_n \leq 50$  A and M8 range for  $I_n > 50$  A
  - Fixing screws
  - Insulating shields (2 for 3P and 3 for 4P)
- Fixed thermal and magnetic
- Conform to IEC 60947-2, in compliance with NEMA

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.127\)](#)
- [Technical page \(p.128\)](#)
- [DRXTM 125](#)