

CAT. N° 0 275 35



## CAM SWITCH - AMMETER - PR 12 - 16 A - 9 CONTACTS - 3 INDEPENDANT CT - SCREW FIXING

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,521
Weight (g)	183,00

### Product characteristics

#### Function: selective measurement switches

##### Ammeters

- Range : PR 12
- Max. rating AC 21 : 16 A
- Number of contacts : 9
- Function : 3 C.T. with common point without C.T. 3 independent C.T.

### General characteristics

#### Cam switches screw fixing on door

- For selecting and changing the status of the circuits into which it is integrated
- For viewing the state of equipment according to the position of the selector lever
- Mounting on enclosure doors
- Contacts with positive opening and double breaking of poles
- Presentation: grey/black selector lever - aluminium faceplate with marking
- Conform to standards IEC EN 60947-3
- Approved to UL-CSA (USA - Canada)
- IP 40 at front of enclosure (selector lever)
- IP 2X at back of enclosure up to PR 26

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.358-359\)](#)

#### Agreements & certificates of conformity

- [CSA-1725160](#)
- [QC / CB-FR 60026094B](#)
- [UL recogn-280206-E57817](#)

#### Installation instructions & related documents

- [096897001-01](#)