

CAT. N° 0 277 64



## CAM SWITCH - CHANGEOVER SWITCH WITHOUT OFF - PR 40 - 4P - 50 A - BOX 135X170 MM

Pack (number of units)	1
Volume (dm <sup>3</sup> )	6,303
Weight (g)	1 693,00

### Product characteristics

#### Function: changeover switches

##### Without off - 135 x 170 mm box

- Number of poles : 4
- Range : PR 40
- Max. rating AC 21 : 50 A
- Number of contacts : 8

### General characteristics

#### Cam switches insulating box

- For selecting and changing the status of the circuits into which it is integrated
- For viewing the state of equipment according to the position of the selector lever
- Boxed device, class II
- Contacts with positive opening and double breaking of poles
- Presentation: black or grey/black selector lever, faceplate with marking
- Conform to standards IEC EN 60947-3
- IP 65 for 76 x 76 and 96 x 120 mm boxes
- IP 55 for 135 x 170 mm boxes

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.356\)](#)
- [Technical page \(p.357\)](#)
- [Technical page \(p.358-359\)](#)