

CAT. N° 0 280 19



AIR CIRCUIT BREAKER DMX³ 1600 LCU 42 KA - DRAW-OUT VERSION - 4P - 800 A

Pack (number of units)	1
Volume (dm ³)	107,653
Weight (g)	56 412,00

Product characteristics

Draw-out version

- Supplied with
 - 4 auxiliary contacts: NO/NC
 - draw-out base and kit
 - rear orientable terminals for horizontal and vertical connection with bars
 - door sealing

Breaking capacity Icu 42 kA (415 V~)

- Frame 1600
- 4P
- In : 800 A

General characteristics

Air circuit breakers DMX³ 1600 - from 630 to 1600 A

- Automatic air circuit breakers must be equipped with DMX³ 1600 electronic protection units Cat.No 0 281 64/65/66, imperatively ordered together for factory assembly
- Please ask for DMX³ order form
- Conform to IEC 60947-2

Documentation

Catalogue pages & additional information

- [Description page \(p.156\)](#)
- [DMX3 1600 and DMX3-I 1600 - Frame 1600](#)
- [DMX3 1600 electronic protection units](#)

Installation & technical data

- [LE10707AA](#)

Installation instructions & related documents

- [LE08437AC](#)