

CAT. N° 0 287 25



AIR CIRCUIT BREAKER DMX³ 2500 LCU 50 KA - DRAW-OUT VERSION - 3P - 2000 A

Pack (number of units)	1
Volume (dm ³)	192,421
Weight (g)	65 400,00

Product characteristics

Draw-out version

- Supplied with:
 - 4 auxiliary contacts: NO/NC
 - draw-out base and kit
 - flat rear terminals for connection with bars
 - door sealing

DMX³ - N 2500

- Breaking capacity Icu 50 kA (415 V~)
- Frame 2500
- 3P
- In : 2000 A

General characteristics

Air circuit breakers DMX³ 2500 and 4000 - from 800 to 4000 A

- Automatic air circuit breakers must be equipped with electronic protection unit, imperatively ordered together for factory assembly
- Please ask for DMX³ order form
- Conform to IEC 60947-2

Documentation

Catalogue pages & additional information

- [Description page \(p.160\)](#)
- [DMX3 - frame 2500, 4000 & 6300](#)
- [DMX3 - electronic protection units](#)

Installation & technical data

- [Y2687H](#)
- [F01800EN-02_DMX32500_v1](#)
- [Y2958H](#)

Installation instructions & related documents

- [Y2762C](#)

Agreements & certificates of conformity

- [OC / CB - 58365](#)