

CAT. N° 0 300 07

**MINI-TRUNKING DLPLUS - 20X12.5 MM - WITH PARTITION - L 2.1 M - WHITE**

Pack (number of units)	120
Volume (dm ³)	39
Weight (g)	15 800,00

Product characteristics**Mini-trunking**

- EN 50085-2-1 approved

With central partition

- 20 x 12.5
- Length 2.10 m

General characteristics**DLPlus mini-trunking 20 x 12.5 and 32 x 12.5 - profiles and finishing accessories****Documentation****Catalogue pages & additional information**

- [Selection chart \(p.796\)](#)
- [Description page \(p.798\)](#)
- [DLPlus mini-trunking](#)

**Agreements & certificates of conformity**

- [NF 004-NF 593021O](#)

**Installation & technical data**

- [F00988EN-03](#)

**Environmental product profile**

- [LGRP-01349-V01](#)