

REF . 0 300 08

**MINI-TRUNKING DLPLUS - 20X12.5 MM - WITHOUT PARTITION - L 2.1 M - WHITE**

Emballage (nombre number of units)	120
Volume (dm ³)	39
Poids (g)	14 500,00

Caractéristiques du produit**Mini-trunking**

- EN 50085-2-1 approved

Without central partition

- Mini-trunking with cable grip
- Equipped with an integrated device for holding cables in place
- Length 2.10 m
- 20 x 12.5
- Without adhesive

Caractéristiques générales**DLPlus mini-trunking 20 x 12.5 and 32 x 12.5 - profiles and finishing accessories****Documentation associée****Catalogue pages & additional information**

- [Selection chart \(p.796\)](#)
- [Description page \(p.798\)](#)
- [DLPlus mini-trunking](#)

**Agreements & certificates of conformity**

- [NF 004-NF 593021O](#)

**Installation & technical data**

- [F00988EN-03](#)

**Environmental product profile**

- [LGRP-01349-V01](#)