

CAT. N° 0 319 10

**CABLE TIE COLSON - UV PROTECTED - EXTERNAL TEETH - WIDTH 9 MM - L. 123 MM - BLACK**

Pack (number of units)	O/R
Volume (dm <sup>3</sup> )	O/R
Weight (g)	O/R

**Product characteristics****Black Colson U.V. protected cable ties - New design**

- New design for installation with less effort
- Conform to EN 50146 and IEC 62275

**External teeth**

- New packaging offering several places to access the cable ties and hanging options (except Cat.No 0 319 21)
- Width : : 9 mm
- Flat length : : 123 mm
- Ø grip capacity max. : : 22 mm
- Ø grip capacity min. : : 4 mm
- Tensile Strength : : 36 kg

**General characteristics****Colson™ - installation cable ties****Documentation** **Catalogue pages & additional information**

- [Description page \(p.627\)](#)
- [Technical page \(p.628\)](#)

 **Installation & technical data**

- [F00139EN-10](#)
- [F002529EN-00](#)