

CAT. N° 0 319 16

## CABLE TIE COLSON - UV PROTECTED - EXTERNAL TEETH - WIDTH 9 MM - L. 262 MM - BLACK



Pack (number of units)	O/R
Volume (dm <sup>3</sup> )	O/R
Weight (g)	O/R

### Product characteristics

#### Black Colson U.V. protected cable ties - New design

- New design for installation with less effort
- Conform to EN 50146 and IEC 62275

#### External teeth

- New packaging offering several places to access the cable ties and hanging options (except Cat.No 0 319 21)
- Width : : 9 mm
- Flat length : : 262 mm
- Ø grip capacity max. : : 62 mm
- Ø grip capacity min. : : 26 mm
- Tensile Strength : : 53 kg

### General characteristics

#### Colson™ - installation cable ties

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.627\)](#)
- [Technical page \(p.628\)](#)

#### Environmental product profile

- [LGRP-00673-V01](#)

#### Installation & technical data

- [F00139EN-10](#)
- [F002529EN-00](#)