

CAT. N° 0 319 28

**CABLE TIE COLSON - U.V PROTECTED - INTERNAL TEETH
- WIDTH 7.6 MM - L. 128 MM -BLACK**

Pack (number of units)	100
Volume (dm ³)	0,896
Weight (g)	152,00

Product characteristics**Black U.V. protected Colson cable ties**

- Width : : 7.6 mm
- Flat length : : 128 mm
- Ø grip capacity max. : : 22 mm
- Ø grip capacity min. : : 8 mm
- Tensile Strength : : 36 kg

General characteristics**Colson™ - installation cable ties****Documentation****Catalogue pages & additional information**

- [Description page \(p.627\)](#)
- [Technical page \(p.628\)](#)

**Environmental product profile**

- [LGRP-00673-V01](#)