

CAT. N° 0 321 00



LCS³ 19" MODULAR OPTIC DRAWER - SLIDING - TO BE EQUIPPED WITH FIBRE OPTIC BLOCKS - 4 BLOCKS MAXIMUM

Pack (number of units)	2
Volume (dm³)	44,574
Weight (g)	7 455,00

Product characteristics

Flat and angled 19" modular fibre optic drawers

- Metal 19" modular fibre optic drawers, 8 cable entries, supplied with 2 cable glands (Ø 13.5 and 9 mm), coiling system
- Equipped with the new-generation Quick-Fix system for automatic (screwless) mounting on enclosure or cabinet uprights
- Supplied with numbered labels
- Maximum capacity: 96 fibres in LC version, 48 in SC version or 24 in ST version
- Depth 290 mm, height 1U

Sliding, to be equipped with fibre optic blocks

- Takes any fibre optic block, up to 4 blocks maximum
- End stop at a 20° angle
- Empty drawer

General characteristics

Legrand cabling system, LCS³ fibre optic - 19" fibre optic drawers

Documentation



Video

- [DI_isere_0009_optical_modular_fiber_pan](#)
- [DI_isere_0011_quick_fix_optical_fiber](#)



Installation instructions & related documents

- [LE09845AD](#)



Documents & videos

- [DI_isere_0009_optical_modular_fiber_pan](#)
- [DI_isere_0011_quick_fix_optical_fiber](#)



Catalogue pages & additional information

- [Selection chart \(p.714\)](#)
- [Description page \(p.747\)](#)



Installation & technical data

- [S000099289EN-04](#)