

CAT. N° 0 321 04



LCS³ 19" MODULAR OPTIC DRAWER - SLIDING - EQUIPPED - 24 LC DUPLEX MULTIMODE CONNECTORS FOR 48 FIBRES

Pack (number of units)	2
Volume (dm³)	44,574
Weight (g)	7 743,00

Product characteristics

Flat and angled 19" modular fibre optic drawers

- Metal 19" modular fibre optic drawers, 8 cable entries, supplied with 2 cable glands (Ø 13.5 and 9 mm), coiling system
- Equipped with the new-generation Quick-Fix system for automatic (screwless) mounting on enclosure or cabinet uprights
- Supplied with numbered labels
- Maximum capacity: 96 fibres in LC version, 48 in SC version or 24 in ST version
- Depth 290 mm, height 1U

Sliding, equipped

- End stop at a 20° angle
- LC duplex for 48 multimode fibres

General characteristics

Legrand cabling system, LCS³ fibre optic - 19" fibre optic drawers

Documentation

Video

- [DI_isere_0009_optical_modular_fiber_pan](#)
- [DI_isere_0011_quick_fix_optical_fiber](#)

Installation instructions & related documents

- [LE09845AD](#)

Documents & videos

- [DI_isere_0009_optical_modular_fiber_pan](#)
- [DI_isere_0011_quick_fix_optical_fiber](#)

Catalogue pages & additional information

- [Selection chart \(p.714\)](#)
- [Description page \(p.747\)](#)

Installation & technical data

- [S000099289EN-04](#)