

CAT. N° 0 325 10



FIBRE CABLE - OM 3 - 900 MM TIGHT BUFFER - INDOOR/OUTDOOR - 6 FIBRES

Pack (number of units)	2000
Volume (dm ³)	1140
Weight (g)	108 900,00

Product characteristics

Multimode OM3 fibre optic cables (50/125 µm)

- For 50/125 µm multimode installations, OM3 type
- Suitable for 10 Gb Ethernet networks
- Bend insensitive

Indoor/Outdoor

- Aqua LSZH sheath
- Glass strands
- Euroclass Dca
- Tight-buffer 900 µm
- 6 fibres

General characteristics

Legrand cabling system LCS³ fibre optic - cables

- Colour code: FOTAG
- Compliant with EN 50173-2 and ISO IEC 11801 standards
- Packed on a 2000 m reel except for tight-buffer OM4
- Tight-buffer: "easy strip"
- Other configurations on request

Documentation



Catalogue pages & additional information

- [Selection chart \(p.719\)](#)
- [Description page \(p.746\)](#)
- [Technical page \(p.777\)](#)



Environmental product profile

- [LGRP-00839-V01](#)



Installation & technical data

- [F01074EN-06](#)