

CAT. N° 0 325 40



## LCS<sup>3</sup> OM3 MULTIMODE FIBRE OPTIC CABLES - LOOSE TUBE - OUTDOOR - CORRUGATED STEEL TAPE - 8 FIBRES - 2000 M

Pack (number of units)	2000
Volume (dm <sup>3</sup> )	1368
Weight (g)	199 000,00

### Product characteristics

#### Multimode OM3 fibre optic cables (50/125 µm)

- For 50/125 µm multimode installations, OM3 type
- Suitable for 10 Gb Ethernet networks
- Bend insensitive

#### Outdoor

- Black PE sheath
- Glass strands for rodent-proofing, reinforced with corrugated steel
- Loose tube
- 8 fibres

### General characteristics

#### Legrand cabling system LCS<sup>3</sup> fibre optic - cables

- Colour code: FOTAG
- Compliant with EN 50173-2 and ISO IEC 11801 standards
- Packed on a 2000 m reel except for tight-buffer OM4
- Tight-buffer: "easy strip"
- Other configurations on request

### Documentation



#### Catalogue pages & additional information

- [Selection chart \(p.719\)](#)
- [Description page \(p.746\)](#)
- [Technical page \(p.777\)](#)



#### Installation & technical data

- [S000099474EN-02](#)