

CAT. N° 0 326 96

**PATCH CORD FIBRE OPTIC LCS³ - OM4 MULTIMODE (50/125MM) - LC/LC UNIBOOT DUPLEX - REVERSIBLE POLARITY - 2 M**

Pack (number of units)	3
Volume (dm ³)	2,948
Weight (g)	144,00

Product characteristics**OM4 multimode fibre optic cords (50/125 µm)**

- Suitable for 10 Gb Ethernet networks
- Max. optical losses/Master: 0.15 dB
- For 50/125 µm multimode installation, OM4 type
- Aqua sheaths

LC/LC Uniboot duplex cords

- Reversible polarity
- Length: 2 m

General characteristics**Legrand cabling system, fibre optic LCS³ - patch cords and feedthrough sockets**

- Fitted at each end with 2 connectors with ceramic ferrule. Individually packed and tested (report supplied)
- LSZH Zipcord sheath
- Other configurations on request

Documentation**Catalogue pages & additional information**

- [Selection chart \(p.719\)](#)
- [Description page \(p.751\)](#)

**Installation & technical data**

- [S000100293EN-00](#)