

CAT. N° 0 340 43



LINE TAP - NON-SHEAR - WITH FEET - CAPACITY PER TAP 2X25 MM² - HEXAGONAL HEAD

Pack (number of units)	20
Volume (dm ³)	1,164
Weight (g)	953,00

Product characteristics

Line taps

Non-shear line taps

- Hexagonal head
- With feet
- Capacity per tap: : 2 x 25 mm²
- Width of slot: : 7.4 max. cable Ø in mm
- Overall height : : 49 mm
- Fixing centres: : 37 mm

General characteristics

Line taps and equipotential bonding connectors

Documentation



Catalogue pages & additional information

- [Description page \(p.631\)](#)



Installation & technical data

- [F00003-01en](#)