

CAT. N° 0 342 15

CONNECTION STRIP NYLBLOC - CAPACITY 10 MM² - MAX. CURRENT 57 A - BLACK



Pack (number of units)	200
Volume (dm ³)	15
Weight (g)	9 281,00

Product characteristics

Nylbloc connection strips

- 12 elements with captive screws
- Supplied with screws undone
- Flame retardant polypropylene (– 25 °C to + 100 °C)
- Ambient temperature from – 25 °C to + 55 °C (T 55)
- Conform to EN 60998-2-1 and EN 60664-1
- Self-extinguishing to EN 60695-2-11 at 850
- Insulation voltage: 250 V according to EN 60 998-2-1
- Use at 400 V integrated in a series of products that comply with the requirements of EN 60664-1, pollution degree 2, overload category III
- Black
- Rated capacity: : 10 mm²
- Hole Ø : : 4.5 mm
- Max current : : 57 A

General characteristics

Nylbloc™ - connection strips and connectors without screws

Documentation



Catalogue pages & additional information

- [Description page \(p.630\)](#)



Agreements & certificates of conformity

- [KEMA - 2171325.02](#)
- [NF - 650672A](#)
- [VDE - 40018574](#)
- [AENOR - 030/000810](#)
- [IMQ - EN642](#)