

CAT. N° 0 353 06



RESISTANCE HEATER - FOR ENCLOSURE - 120/240 V~/= - 20 W

Pack (number of units)	1
Volume (dm ³)	0,485
Weight (g)	197,00

Product characteristics

Heating

- IP 20
- Class II
- Prevent condensation forming inside the enclosure «PTC» auto-regulated and self-limited surface temperature
- Connection on terminals
- Mounting on rail
- Heat dissipator in aluminium under plastic UL 94 VO

Resistance heaters 120 V/240 V~/=

- Power : 20 W
- Start-up current : 2.5 A

General characteristics

Heat regulation for cabinets and enclosures - heating and regulation

Documentation



Catalogue pages & additional information

- [Description page \(p.314\)](#)
- [Heat regulation for cabinets and enclosures](#)