

CAT. N° 0 362 63


CABINET MARINA - POLYESTER - IP66 - IK10 - 1020X810X300 MM

| | |
|---------------------------|-----------|
| Pack (number of units) | 1 |
| Volume (dm ³) | 273 |
| Weight (g) | 28 400,00 |

Product characteristics
RAL 7035 cabinets

- External dimensions Height x Width x Depth : 1020 x 810 x 300 mm
- Corresponding metal cabinets Height x Width x Depth : 1000 x 800 x 300 mm

General characteristics
Marina cabinets - polyester - IP 66 - IK 10

- IP 66 according to IEC EN 60529. LCIE n°60059283-560528
- IK 10 according to IEC EN 62262 (EN 50102)
- Class II (used to create totally isolated assemblies acc. to EN 60439-1 and assemblies for photovoltaic installations acc. to UTE C15-712-1)
- Fiber glass reinforced polyester. Self-extinguishing 960°C acc. to IEC EN 60695-2-11
- Adapted to corrosive environment and different weather conditions (detailed technical sheet available on e-catalogue)
- Reversible door, opening 180°, (except Cat.No 0 362 50). Stainless steel hinge pins (except Cat.No 0 362 50). 2 double bar lock (1 lock for Cat.No 0 362 50)
- Direct fixing of equipment at bottom of cabinet (screws supplied)
- Possible to fit a partial plate from 500 x 400 x 200 mm and/or rails on intermediate studs (except for Cat.No 0 362 50)
- Optional depth adjustment from height 400 x width 300 mm with Cat.No 0 362 42
- Can be equipped with Atlantic accessories

Documentation

Catalogue pages & additional information

- [Selection chart \(p.288-289\)](#)
- [Description page \(p.297\)](#)
- [Technical page \(p.301\)](#)
- [Technical page \(p.302\)](#)


Installation & technical data

- F00635EN-03


Installation instructions & related documents

- [LE08303AA-01](#)


Agreements & certificates of conformity

- VERITAS (BV) - 07327/DO BV