

CAT. N° 0 362 72


**CABINET MARINA - POLYESTER WITH GLASS DOOR - IP66
- IK10 - 500X400X206 MM**

Pack (number of units)	1
Volume (dm ³)	66
Weight (g)	6 200,00

Product characteristics
RAL 7035 cabinets with glass door

- Coloured toughened glass
- External dimensions Height x Width x Depth : 500 x 400 x 206 mm
- Window dimensions Height x Width : 335 x 245 mm

General characteristics
Marina cabinets - polyester - IP 66 - IK 10

- IP 66 according to IEC EN 60529. LCIE n°60059283-560528
- IK 10 according to IEC EN 62262 (EN 50102)
- Class II (used to create totally isolated assemblies acc. to EN 60439-1 and assemblies for photovoltaic installations acc. to UTE C15-712-1)
- Fiber glass reinforced polyester. Self-extinguishing 960°C acc. to IEC EN 60695-2-11
- Adapted to corrosive environment and different weather conditions (detailed technical sheet available on e-catalogue)
- Reversible door, opening 180°, (except Cat.No 0 362 50). Stainless steel hinge pins (except Cat.No 0 362 50). 2 double bar lock (1 lock for Cat.No 0 362 50)
- Direct fixing of equipment at bottom of cabinet (screws supplied)
- Possible to fit a partial plate from 500 x 400 x 200 mm and/or rails on intermediate studs (except for Cat.No 0 362 50)
- Optional depth adjustment from height 400 x width 300 mm with Cat.No 0 362 42
- Can be equipped with Atlantic accessories

Documentation
 **Catalogue pages & additional information**

- [Selection chart \(p.288-289\)](#)
- [Description page \(p.297\)](#)
- [Technical page \(p.301\)](#)
- [Technical page \(p.302\)](#)

 **Installation & technical data**

- F00635EN-03

 **Installation instructions & related documents**

- [LE08303AA-01](#)

 **Agreements & certificates of conformity**

- [VERITAS \(BV\) - 07327/E0 BV](#)