

CAT. N° 0 362 87


**ENCLOSURE MARINA - POLYESTER - IP66 - IK10 - 1860X800X463 MM**

Pack (number of units)	1
Volume (dm <sup>3</sup> )	905
Weight (g)	65 800,00

**Product characteristics**
**Enclosures RAL 7035**

- External dimensions Height x Width x Depth : 1860 x 800 x 463 mm
- Corresponding metal enclosures Height x Width x Depth : 1800 x 800 x 400 mm

**General characteristics**
**Marina enclosures - polyester - IP 66 - IK 10**

- IP 66 acc. to IEC EN 60529. LCIE n° 60059283-560528
- IK 10 acc. to EN 62262 (EN 50102)
- Class II (Used to create totally isolated assemblies acc. to EN 60439-1)
- Fiberglass reinforced polyester. Self-extinguishing 960°C acc. to IEC EN 60695-2-11
- Adapted to corrosive environment. Supplied with fixing kit for plain plates or sectionned uprights
- Depth adjustment of equipment
- Equipped with low cable entries plate
- Reversible door with strand-holder
- 3 point closing with handle fitted with 1/2 locking latch 2433 A (other key code, please consult us)
- Stainless steel hinges and hinges axis

**Documentation**
 **Catalogue pages & additional information**

- [Description page \(p.299\)](#)
- [Technical page \(p.301\)](#)
- [Technical page \(p.302\)](#)

 **Installation & technical data**

- [F01090EN-01](#)

 **Installation instructions & related documents**

- [041650-02](#)

 **Agreements & certificates of conformity**

- [VERITAS \(BV\) - 07327/E0 BV](#)