

CAT. N° 0 369 46



ATLANTIC METAL CABINET - VERTICAL VERSION - 1200 X 800 X 400 MM - 1 DOOR

Pack (number of units)	1
Volume (dm ³)	480,975
Weight (g)	76 000,00

Product characteristics

Metal door cabinets

- Supplied with plain plate

Vertical version

- External dimensions Height x Width x Depth : 1200 x 800 x 400 mm
- Number of doors : 1
- Weight : 73.6 kg

General characteristics

Atlantic metal cabinets supplied with plain plate - IP 55/IP 66 - IK 10 - Type 4x - Type 12

- IP 66 according to standards IEC EN 60529 for 1-door cabinets - IP 55 according to standards IEC EN 60529 for 2-door cabinets
- IK 10 according to standards IEC EN 62262
- LCIE 17 07 90 10A
- Type 4x, 1 door, Type 12, 2 doors - cULus, Bureau Veritas
- EMC attenuation 20 dB (for an EMC attenuation from 40 to 50 dB at 1 GHz, please consult us)
- Excellent resistance to corrosion and chemical agents
- 80 µm thick textured polyester coating. Anti-corrosion treatment for hinges and pins
- Reversible door - Fitted with lever
- Supplied with double bar lock - Self-centering positioning system for the equipment
- Compatible with all Atlantic accessories Low cable entries RAL 7035 - Optional depth adjustment for cabinets 400 mm depth, with slide rails Cat.No 0 367 45

Documentation

Catalogue pages & additional information

- [Selection chart \(p.288-289\)](#)
- [Description page \(p.290\)](#)
- [Technical page \(p.295\)](#)
- [Technical page \(p.296\)](#)

Installation & technical data

- [F02118EN-02](#)

Installation instructions & related documents

- [LE08301AA-01](#)

Agreements & certificates of conformity

- [VERITAS \(BV\) - 03212/I0 BV](#)
- [TUV GS - R60135228](#)
- [UL listed cULus - E164087-19951122](#)
- [OC / CB - FR703246](#)