

CAT. N° 0 369 78



## ATLANTIC METAL CABINET - HORIZONTAL VERSION - 600 X 800 X 300 MM - 2 DOORS

Pack (number of units)	1
Volume (dm <sup>3</sup> )	205,103
Weight (g)	32 600,00

### Product characteristics

#### Metal door cabinets

- Supplied with plain plate

#### Horizontal version

- External dimensions Height x Width x Depth : 600 x 800 x 300 mm
- Number of doors : 2
- Weight : 38.4 kg

### General characteristics

#### Atlantic metal cabinets supplied with plain plate - IP 55/IP 66 - IK 10 - Type 4x - Type 12

- IP 66 according to standards IEC EN 60529 for 1-door cabinets - IP 55 according to standards IEC EN 60529 for 2-door cabinets
- IK 10 according to standards IEC EN 62262
- LCIE 17 07 90 10A
- Type 4x, 1 door, Type 12, 2 doors - cULus, Bureau Veritas
- EMC attenuation 20 dB (for an EMC attenuation from 40 to 50 dB at 1 GHz, please consult us)
- Excellent resistance to corrosion and chemical agents
- 80 µm thick textured polyester coating. Anti-corrosion treatment for hinges and pins
- Reversible door - Fitted with lever
- Supplied with double bar lock - Self-centering positioning system for the equipment
- Compatible with all Atlantic accessories Low cable entries RAL 7035 - Optional depth adjustment for cabinets 400 mm depth, with slide rails Cat.No 0 367 45

### Documentation

#### Catalogue pages & additional information

- [Selection chart \(p.288-289\)](#)
- [Description page \(p.290\)](#)
- [Technical page \(p.295\)](#)
- [Technical page \(p.296\)](#)

#### Installation & technical data

- [F02118EN-03](#)

#### Environmental product profile

- [LGRP-2015-020-V1-EN](#)

#### Installation instructions & related documents

- [LE08301AA-01](#)

#### Agreements & certificates of conformity

- [TUV GS-R60135228](#)
- [UL listed cULus-E164087-19951122](#)
- [VERITAS \(BV\)-03212/J0 BV](#)
- [OC / CB-FR703246](#)