

CAT. N° 0 371 55

**TERMINAL BLOCK VIKING 3 - SCREW - FUNCTION BLOCK  
- 1 CONNECT - MODULAR - PITCH 6**

Pack (number of units)	60
Volume (dm <sup>3</sup> )	2,094
Weight (g)	1 077,00

**Product characteristics****Function blocks****2 connections on 2 levels - diode carrier**

- Colour : Grey
- Nominal cross-section : 4 mm<sup>2</sup>
- Capacity – Rigid wire : 0.25 to 6 mm<sup>2</sup>
- Capacity – Flexible wire with or without ferrules : 0.25 to 4 mm<sup>2</sup>
- Pitch : 6 mm

**General characteristics****Viking™ 3 terminal blocks with screw connection - for copper cables**

- Used to make the electrical connection between 2 flexible copper wires with or without ferrules or 2 rigid copper wires
- 2 areas for automatic insertion bridging combs up to 8 pitch (upper level only for multi-level blocks)
- For rails depth 15 mm, EN 60715 depth 7.5 mm and 15 mm

**Documentation****Catalogue pages & additional information**

- [Selection chart \(p.324-325\)](#)
- [Description page \(p.329\)](#)
- [Technical page \(p.335\)](#)
- [Viking™ 3 terminal blocks with screw connection](#)

**Agreements & certificates of conformity**

- NF App Industri - NF208\_1010
- UL recogn - 20101029-E60900
- VERITAS (BV) - 23393/BO BV
- IMQ - CA02\_04204