

CAT. N° 0 371 74



## TERMINAL BLOCK VIKING 3 -SCREW -FR CONDUCTOR -1 CONNECTION -METAL BASE -PITCH 12

Pack (number of units)	10
Volume (dm <sup>3</sup> )	0,836
Weight (g)	611,00

### Product characteristics

#### For protection conductor

- Metal base

#### 1 connection - 1 entry/1 outlet

- Screwless fixing on rail up to 10 mm pitch and with screws for pitch 12 and 15 mm
- PEN from 10 mm<sup>2</sup>
- Colour : Green/yellow
- Nominal cross-section : 16 mm<sup>2</sup>
- Capacity – Rigid wire : 1.5 to 25 mm<sup>2</sup>
- Capacity – Flexible wire with or without ferrules : 4 to 16 mm<sup>2</sup>
- Pitch : 12 mm

### General characteristics

#### Viking™ 3 terminal blocks with screw connection - for copper cables

- Used to make the electrical connection between 2 flexible copper wires with or without ferrules or 2 rigid copper wires
- 2 areas for automatic insertion bridging combs up to 8 pitch (upper level only for multi-level blocks)
- For rails depth 15 mm, EN 60715 depth 7.5 mm and 15 mm

### Documentation

#### Catalogue pages & additional information

- [Selection chart \(p.324-325\)](#)
- [Description page \(p.328\)](#)
- [Technical page \(p.335\)](#)
- [Viking™ 3 terminal blocks with screw connection](#)

#### Agreements & certificates of conformity

- [IMQ-CA02](#)
- [VERITAS \(BV\)-23393/C0 BV](#)
- [NF App Industri-NF208\\_1008](#)
- [UL recogn-20101029-E60900](#)
- [ATEX-LCIE 16 ATEX 3049U - 02](#)
- [Ex-002/H](#)

#### Installation & technical data

- [F00671EN-02](#)
- [F00914EN-00](#)
- [F00914EN-01](#)