

CAT. N° 0 372 64



TERMINAL BLOCK VIKING 3 - SPRING - 1 CONNECT - 1 ENTRY/1 OUTLET - PITCH 12 -GREY

Pack (number of units)	10
Volume (dm ³)	0,626
Weight (g)	365,00

Product characteristics

Connecting

- Grey for standard circuit, blue for neutral conductor, orange for circuit not broken by the master isolating device

1 connection - 2 wires - 1 entry/1 outlet

- Built-in end cap
- Colour : Grey
- Nominal cross-section : 16 mm²
- Capacity - Rigid wire : 4 to 16 mm²
- Capacity - Flexible wire : 4 to 16 mm²
- Flexible wire with ferrule : 4 to 16 mm²
- Pitch : 12 mm

General characteristics

Viking™ 3 terminal blocks with spring connection - for copper cables

- Screwless connection system, stainless steel spring type
- Used to make the electrical connection between 2 rigid copper wires, or flexible copper wires with or without ferrules
- Direct tool-free insertion of a rigid wire or flexible wire with ferrule, up to 6 mm pitch
- 2 areas for automatic insertion bridging combs (upper level only for 2-level blocks)
- For rails depth 15 mm, EN 60715 depth 7.5 mm and 15 mm

Documentation

Catalogue pages & additional information

- [Selection chart \(p.326-327\)](#)
- [Description page \(p.330\)](#)
- [Technical page \(p.336\)](#)
- [Viking™ 3 terminal blocks with spring connection](#)

Agreements & certificates of conformity

- [UL recogn-20100921-E60900](#)
- [NF App Industri-NF208_1012](#)
- [VERITAS \(BV\)-23393/C0 BV](#)
- [IMQ-CA02](#)
- [ATEX-LCIE 16 ATEX 3049U - 02](#)
- [Ex-002/H](#)

Installation & technical data

- [F01007EN-02](#)