

CAT. N° 0 374 19

COPPER BAR - FLAT RIGID - SECTION 32 X 5 MM - 400 TO 450 A - L. 1750 MM

Pack (number of units)	4
Volume (dm ³)	1
Weight (g)	9 300,00

Product characteristics**Copper bars****Rigid, flat, threaded holes**

- Cross section : 32 x 5 mm
- I permissible IP ? 30 : 450 A
- I permissible IP > 30 : 400 A
- Holes Ø mm : M6
- Length : 1750 mm

General characteristics**Copper bars and accessories**

- Standard distribution

Documentation**Catalogue pages & additional information**

- [Selection chart \(p.260-261\)](#)
- [Description page \(p.260-261\)](#)
- [Selection chart \(p.282-283\)](#)
- [Description page \(p.282-283\)](#)