

CAT. N° 0 374 33

**COPPER BAR WITH TAPPED HOLES - 15 X 4 MM - MAX.
200 A - L. 990 MM**

Pack (number of units)	10
Volume (dm ³)	1
Weight (g)	4 470,00

Product characteristics**Copper bars****Rigid, flat, threaded holes**

- Cross section : 15 x 4 mm
- I permissible IP ? 30 : 200 A
- I permissible IP > 30 : 160 A
- Holes Ø mm : M6
- Length : 990 mm

General characteristics**Copper bars and accessories**

- Standard distribution

Documentation**Catalogue pages & additional information**

- [Description page \(p.260-261\)](#)
- [Description page \(p.282-283\)](#)