

CAT. N° 0 374 38

COPPER BAR - FLAT RIGID - SECTION 25 X 4 MM - 250 TO 280 A - L. 990 MM

Pack (number of units)	10
Volume (dm ³)	1
Weight (g)	7 830,00

Product characteristics**Copper bars****Rigid, flat, threaded holes**

- Cross section : 25 x 4 mm
- I permissible IP ? 30 : 280 A
- I permissible IP > 30 : 250 A
- Holes Ø mm : M6
- Length : 990 mm

General characteristics**Copper bars and accessories**

- Standard distribution

Documentation**Catalogue pages & additional information**

- [Selection chart \(p.260-261\)](#)
- [Description page \(p.260-261\)](#)
- [Selection chart \(p.282-283\)](#)
- [Description page \(p.282-283\)](#)