

CAT. N° 0 380 00



BREAK GLASS EMERGENCY BOX-MUSHROOM HEAD-SURFACE MOUNTING-IP44-YELLOW BOX W LED

Pack (number of units)	1
Volume (dm ³)	1,515
Weight (g)	441,00

Product characteristics

Break glass emergency boxes

- Polycarbonate, Class II - IK 07
- Equipped with:
 - hinged glass door with locking option by key
 - 3 cable entries for CG ISO 16/20 (by top or bottom as reversible product)
 - 2 entries from back of product Ø20
 - 2 side entries for mini-trunking 20 x 12.5 and 32 x 12.5
 - 1 NC contact and 1 NO contact
- Breaking capacity:
 - 400 V~ / 4.5 A
 - 230 V~ / 6 A
 - 48 V DC / 1 A
 - 24 V DC / 1.5 A
- Flush-mounting option with boxes Ø85
- Dim.: 125 x 125 x 71 mm (surface-mounting) IP 44 - 125 x 125 x 33 mm (flush-mounting) IP 30
- Red boxes can be used for fire applications and manipulated by fire fighters
- Yellow boxes can be used for emergency applications and manipulated by employees

Mushroom head button boxes

- Direct actuation by smashing glass plate
- Equipment:
 - 1 mushroom head button with latching, unlocking by key No 850
 - 2 long life 230 V~ LED indicators (green/red)
- Yellow box with LED

General characteristics

Safety boxes 125 series - for emergency applications

Documentation

Catalogue pages & additional information

- [Description page \(p.696\)](#)

Environmental product profile

- [LGRP-00105-V01](#)

Installation instructions & related documents

- [4065388-06](#)