

CAT. N° 0 401 49



ACTIVE POWER COMPENSATOR

Pack (number of units)	1
Volume (dm ³)	0,101
Weight (g)	14,00

Product characteristics

Active Power Compensator

- Makes 2-wire electronic lighting control units without neutral compatible with all commercially-available loads (LED, compact fluorescent, ELV halogen with ferromagnetic or electronic ballast, 230 V halogen, fluorescent tube, incandescent)
- Consumption 0.4 W

General characteristics

Mosaic™ Programme mechanisms - motion and presence sensors

- All sensors are compatible with any lamp - Detection field: 120°
- Detection range: 8 m
- Recommended installation height: 1.20 m
- Integrated self-protection against overloads and short-circuits.
- 2 modules

Documentation

Catalogue pages & additional information

- [Description page \(p.455\)](#)
- [Description page \(p.456\)](#)
- [Description page \(p.496\)](#)
- [Description page \(p.518\)](#)
- [Description page \(p.531\)](#)
- [Description page \(p.549\)](#)
- [Description page \(p.553\)](#)
- [Description page \(p.555\)](#)
- [Description page \(p.562\)](#)
- [Description page \(p.570\)](#)
- [Description page \(p.590\)](#)
- [Description page \(p.880\)](#)
- [Belanko™ - dimmers and ventilation control](#)

Installation & technical data

- [F02436EN-02](#)

Installation instructions & related documents

- [LE09710AB](#)