

CAT. N° 0 415 36



ELECTROMECHANICAL SIREN - IP30 - IK05 - 24 V~ - 12.5 W- 531 MA

Pack (number of units)	1
Volume (dm ³)	1,315
Weight (g)	245,00

Product characteristics

Electromechanical sirens IP 30 - IK 05

- Supplied with screws for semi-flush mounting

A.C. current - 50/60 Hz

- Voltage : 24 V~
- Power : 12.5 W
- Consumption : 531 mA
- Average acoustic output at 1 m : 100 dB
- Weight : 0.2 kg
- Max. continuous rating : 200 hr

General characteristics

Electromechanical and electronic sirens

Documentation

Catalogue pages & additional information

- [Description page \(p.394\)](#)
- [Technical page \(p.395a\)](#)

Mélodie, son, sonnerie

- [41539](#)

Installation instructions & related documents

- [4065212-04](#)