

CAT. N° 0 415 38

**ELECTROMECHANICAL SIREN - IP30 - IK05 - 110 V~ - 70 W- 400 MA**

Pack (number of units)	1
Volume (dm ³)	1,315
Weight (g)	439,00

Product characteristics**Electromechanical sirens IP 30 - IK 05**

- Supplied with screws for semi-flush mounting

A.C. current - 50/60 Hz

- Voltage : 110 V~
- Power : 70 W
- Consumption : 400 mA
- Average acoustic output at 1 m : 105 dB
- Weight : 0,35 kg
- Max. continuous rating : 100 hr

General characteristics**Electromechanical and electronic sirens****Documentation****Catalogue pages & additional information**

- [Description page \(p.394\)](#)
- [Technical page \(p.395a\)](#)

**Installation instructions & related documents**

- [4065212-04](#)