

CAT. N° 0 415 39


**ELECTROMECHANICAL SIREN - IP30 - IK05 230 V~ - 57 W-250 MA**

Pack (number of units)	1
Volume (dm <sup>3</sup> )	1,315
Weight (g)	448,00

**Product characteristics**
**Electromechanical sirens IP 30 - IK 05**


- Supplied with screws for semi-flush mounting

**A.C. current - 50/60 Hz**

- Voltage : 230 V~
- Power : 57 W
- Consumption : 250 mA
- Average acoustic output at 1 m : 105 dB
- Weight : 0,35 kg
- Max. continuous rating : 100 hr

**General characteristics**
**Electromechanical and electronic sirens**
**Documentation**
 **Catalogue pages & additional information**

- [Description page \(p.394\)](#)
- [Technical page \(p.395a\)](#)

 **Mélodie, son, sonnerie**

- [41539](#)

 **Installation instructions & related documents**

- [4065212-04](#)