

CAT. N° 0 462 23

FIXED SHELF - FOR 10" CABINET - 1 U - DEPTH 120 MM



Pack (number of units)	1
Volume (dm ³)	3,218
Weight (g)	450,00

Product characteristics

Equipment for 10" cabinets

Panels and shelves

- Fixed shelf 1 U
- Depth 120 mm
- Max. load. 10 kg
- Black RAL 9005
- Supplied with screws and cage nuts

General characteristics

Linkeo 19" and 10" wall-mounting cabinets

- IP 20 - IK 08
- Equipped with:
 - 1 reversible door made of screen-printed safety glass and with integrated lock
 - 2 x 19" uprights with U marking and adjustable in depth
 - 3 pre-cut cable entries (top, bottom and rear). 1 brush for a cable entry. Top perforations for natural ventilation
 - panels with automatic grounding (ready assembled version)
 - earthing kit (flatpack version)
- Anthracite grey RAL 7016

Documentation



Catalogue pages & additional information

- [Description page \(p.784\)](#)
- [Technical page \(p.790\)](#)
- [Technical page \(p.791\)](#)



Installation & technical data

- [F02825EN-00](#)