

CAT. N° 0 473 62



19" 42 U ALTIS CABINET WITH FRAMED GLASS DOOR - 2000 X 600 X 600 MM

Pack (number of units)	1
Volume (dm ³)	870
Weight (g)	82 600,00

Product characteristics

Altis 19" 42 U cabinets

Cabinets with framed glass door

- Protection against dust, water, knocks in demanding environments - IP55 - IK10
- For loads up to 720 kg on four 19" uprights
- Reversible door with toughened glass window
- 4-point locking with double bar (key barrels Cat.No 0 347 XX)
- Removable rear panel
- Cable entries at bottom (plates Cat.No 0 481 XX)
- Can be equipped with plinth (Cat.No 0 476 XX)
- 19" uprights and side panels to be ordered separately
- Grey RAL 7035
- Dimensions - Height : 2000 mm
- Dimensions - Width : 600 mm
- Dimensions - Depth : 600 mm
- Window dim. - Height : 1775 mm
- Window dim. - Width : 375 mm
- Weight : 91.7 mm

General characteristics

Altis™ 19" freestanding cabinets IP 55 - IK 10

Documentation



Catalogue pages & additional information

- [Description page \(p.795\)](#)



Installation & technical data

- [F00710EN-08](#)



Installation instructions & related documents

- [LE08321AA-00](#)



Agreements & certificates of conformity

- [TUV GS - R60135231 - 002](#)