

CAT. N° 0 491 20



SINGLE POLE LATCHING RELAY - SILENT - 10 A - SURFACE-MOUNTING

Pack (number of units)	10
Volume (dm ³)	0,793
Weight (g)	494,00

Product characteristics

Surface mounting pulse operated latching relays

- 10 A - 230 V~ - 50/60 Hz
- Suitable for new installations or retrofitting of existing ones
- Compatible with electronic ballasts and fluocompact lamps
- Mounting on plate or in flush-mounting boxes Ø 67 mm
- Equipped with automatic terminals for flexible or rigid wires (max. 2.5 mm)
- Power : min. 7 W / max. 2300 W
- IP 20 - IK 04
- Dimensions: 49 x 46 x 26 mm
- Maximum current when used with illuminated push-buttons : 50 mA

Noiseless

- Single pole
- Single pole

General characteristics

Pulse operated latching relays CX³

Documentation

Catalogue pages & additional information

- [Description page \(p.084\)](#)
- [Technical page \(p.085\)](#)
- [Dimensions of din-rail equipment](#)

Agreements & certificates of conformity

- [NF-652488](#)
- [VDE-40026508](#)

Installation instructions & related documents

- [292389-03](#)

Environmental product profile

- [LGRP-2015-187-V1-EN](#)