

CAT. N° 0 502 52



## 2P+E PLUG - 16 A - GERMAN/FR STANDARD - RUBBER - SIDE OUTLET + RING - BULK

Pack (number of units)	10
Volume (dm <sup>3</sup> )	2,363
Weight (g)	570,00

### Product characteristics

#### German standard plugs 16 A - IK 08 and extensions

- Screw terminals
- H07 RNF 3G 2.5 mm<sup>2</sup> max. cable
- Black

#### Plugs

- Bulk
- Side outlet with ring
- Screw cable grip

### General characteristics

#### Rubber single-socket plugs and extensions - German standard

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.636\)](#)

#### Agreements & certificates of conformity

- [OVE - 131-279-05](#)
- [QC / CB - FR 60043450B](#)
- [NF - 636045](#)
- [KSC - JW04005-16002](#)
- [MEEI - UP 69256175 0001](#)
- [QC / CB - 667586](#)

#### Installation & technical data

- [F01040EN-01](#)