

CAT. N° 0 520 49



BOX HYPRA - IP44 - FOR PRISINTER SURFACE MOUNTING SOCKET 2P+E/3P+E 16 A - PLASTIC

Pack (number of units)	1
Volume (dm ³)	1,39
Weight (g)	210,00

Product characteristics

Accessories

For LV prisinter

- Box Hypra
- For plastic prisinter:
 - 100 to 130 V~ 16 A 2P+E
 - 200 to 250 V~ 16 A 2P+E
 - 380 to 415 V~ 16 A 3P+E

General characteristics

Hypra IP 44 sockets and plugs metal, plastic, rubber, IP 44/55 Prisinter - LV 16 to 63 A and ELV 16 and 32 A

- Conform to IEC 60309-1 and IEC 60309-2
- IP 44 according to IEC 60529
- IK 09: plastic and rubber
- IK 10: metal according to IEC 62262
- Self-extinguishing:
 - 850°C (support of active parts) / 960 °C for Prinsinter)
 - 650 °C: plastic housing conform to IEC 60695-2-10
 - 50°C to + 100°C (- 20°C for Prinsinter)

Documentation

Catalogue pages & additional information

- [Selection chart \(p.390-391\)](#)
- [Technical page \(p.392\)](#)
- [Hypra](#)

Installation & technical data

- [F00097EN-05](#)