

CAT. N° 0 524 01



## PANEL MOUNTING SOCKET HYPRA - IP44 - 20/25 V~ - 16 A - 2P - PLASTIC

Pack (number of units)	5
Volume (dm <sup>3</sup> )	2,363
Weight (g)	673,00

### Product characteristics

#### ELV panel mounting sockets

##### 20 to 25 V~ - 50/60 Hz - 16 A 2P

- To be associated with surface-mounting box Cat.No 0 524 19 for surface-mounting socket
- Plastic
- Pack = 5
- 16 A

### General characteristics

#### Hypra IP 44 sockets and plugs metal, plastic, rubber, IP 44/55 Prinsinter - LV 16 to 63 A and ELV 16 and 32 A

- Conform to IEC 60309-1 and IEC 60309-2
- IP 44 according to IEC 60529
- IK 09: plastic and rubber
- IK 10: metal according to IEC 62262
- Self-extinguishing:
  - 850°C (support of active parts) / 960 °C for Prinsinter)
  - 650 °C: plastic housing conform to IEC 60695-2-10
  - 50°C to + 100°C (- 20°C for Prinsinter)

### Documentation

#### Catalogue pages & additional information

- [Selection chart \(p.390-391\)](#)
- [Technical page \(p.392\)](#)
- [Hypra](#)

#### Agreements & certificates of conformity

- [OC / CB-FR\\_710635/A1](#)

#### Installation & technical data

- [F00138EN-03](#)